

Pure C&G AX | Features and Accessories

	7AX	5AX	3AX	2AX	1AX
Dynamic Soundscape Processing 2.0	■■■■■	■■■■■	■■■■■	■■■	■■■
Augmented Focus	✓	✓	✓	✓	✓
Acoustic Sensor	✓	✓	✓	✓	✓
Motion Sensor	✓	✓	✓	—	—
OVP 2.0 (Own Voice Processing) ¹⁾	✓	✓	✓	—	—
Sound Clarity	■■■■■	■■■■■	■■■	■■■	■■■
Signal processing (channels) / Gain&MPO (handles)	48 / 20	32 / 16	24 / 12	16 / 8	16 / 8
Hearing programs	6	6	6	4	4
Extended dynamic range	✓	✓	✓	✓	✓
Speech and noise management	✓	✓	✓	✓	✓
SoundSmoothing	✓	✓	✓	✓	—
Feedback cancellation	✓	✓	✓	✓	✓
HD Music (presets)	3	3	1	1	—
eWindScreen	✓	✓	✓	✓	—
Extended bandwidth	✓	—	—	—	—
Auto EchoShield	✓	—	—	—	—
EchoShield	✓	✓	—	—	—
Speech Quality	■■■■■	■■■■■	■■■	■■■	■■■
Binaural Directionality	✓	✓	✓	—	—
Wireless CROS/BICROS	✓	✓	✓	✓	✓
Frequency compression	✓	✓	✓	✓	✓
Spatial SpeechFocus ^{1) 2)}	✓	✓	—	—	—
Wearer Interaction	■■■■■	■■■■■	■■■■■	■■■■■	■■■■■
Signia Assistant	✓	✓	✓	✓	✓
Signia App (iOS and Android)	✓	✓	✓	✓	✓
Adaptive Streaming Volume ³⁾	✓	✓	✓	✓	✓
Spatial Configurator	✓	✓	—	—	—
Direct Streaming	✓	✓	✓	✓	✓
Android devices (ASHA)	✓	✓	✓	✓	✓
Made for iPhone iPad iPod	✓	✓	✓	✓	✓
HandsFree for iOS	✓	✓	✓	—	—
Tinnitus	✓	✓	✓	✓	—
Notched Amplification Therapy	✓	✓	✓	✓	—
Tinnitus noise therapy signal	✓	✓	✓	✓	—
Fitting	✓	✓	✓	✓	✓
Smart Optimizer and Data Logging	✓	✓	✓	✓	✓
Acclimatization manager	✓	✓	✓	✓	✓
InSituGram	✓	✓	✓	✓	✓
AutoFit	✓	✓	✓	✓	✓
TeleCare	✓	✓	✓	✓	✓
Remote Services	✓	✓	✓	✓	✓
Signia App	✓	✓	✓	✓	✓

¹⁾ req. bilateral fitting

²⁾ for 5AX, right/left directionality available only in Stroll Program and via the Spatial Configurator

³⁾ streaming only

■■■■■ highest feature performance

✓ available — not available ○ optional